


DRAFTING AIDS



Circuit Board Drafting Patterns

An 8-1/2" x 11" sheet containing two dozen of the most commonly used pre-spaced component configurations. Self-adhesive pads may easily be removed from master sheet with printed circuit knife and placed upon Mylar[®] positive artwork. A highly refined process and ink assures true opacity and the excellent definition necessary for quality printed circuit work.

Part No. 21-677



Etch Resist Ink Pens



Black felt tip pens for marking nomenclature and touching up photo artwork or etch resist circuits directly on the PC board or on the positive. Dries instantly. Easy application. Can be removed with Stripping Solution (22-240) or alcohol.

Part No. 22-220	Std. Size – draws lines approx. 1/32" wide
Part No. 22-222	Fine Line – draws lines as thin as 1/64" wide



Exposing Frame

Assures tight contact between positive or negative and the photosensitive material. Results in perfect transfer of circuit image to the board.

Part No. 22-393	For boards up to 10" to 12"
-----------------	-----------------------------

ETCHING

Etching Solution Heater



Fits in tank and heats solution up to 38°C (100°F). Used to further reduce etching time. Built-in adjustable thermostat controls temperature continuously to 100°F. 120V AC/100 W Max.

Part No. 22-392